



This is a sample photo.

ORDER SYMBOL: CAB PC 203018 G

EL.number **EAN:** 6418074020024
Sweden:
Denmark: 8212020401
Finland: 3424103


INCLUDING:
Cabinet body, door with EPDM gasket, hinges, latches, mounting screws, and corner plugs.

APPROVALS:
USA: UL Type 1, 4, 4X, 12, 13 (E75645 Vol. 1 Sec. 6); UL 94-V2

EURO: IP 65; UL 94-V2

OTHERS: IEC 529, EEI

FIBOX CAB PC



CAB 30 20 S

TECHNICAL INFORMATION:

Standard colour: RAL 7035
Ingress protection: IP 65 (IEC 529, EN 60529)
Flame resistance: UL 94-V2

Temp.range in cont. use: Max. +80 °C
Temp. range of material: - 40 °C - + 120 °C

ACCESSORIES

Inspection window	L 02	Ventilation device	MB 10631
Inspection window	L 04		
Inspection window	L 06		
Inspection window	L 08		
Inspection window	L 10		
Inspection window	L 12		
Inspection window	L 12 II		
Inspection window	L 13		
Inspection window	L 24		
Inspection window	L 24 II		