


Quick Links	
RoHS/LF P/N Search	
Documentation	
Customer drawing search	
Free search	
Services	
Distributor list	

[Start](#) > [Search=30220235*](#) > [30220235](#)
30220235
30220235 : 8 way 0.64mm DuoTwin Blue ISO Car Radio

ACTIVE
RoHS Compliant

[Add to Favorites](#)
[Print Datasheet](#)
FCI Brings You More
[✉ Contact our sales/technical support](#)
[✉ Sample request](#)
[Specifications](#)
[Download document](#)
[General](#) [Mechanical](#) [Physical](#) [Terminal 1 Type](#) [Environmental](#) [Other Features](#)
General

Application	Car Radio
Ways	8
Coding version	Blue
Product Type	Housing
Coding	Yes
Features	3 - Module Configuration (6W+6W+8W) Assembles with 6W Green Module 30220235 Suitable for ISO Car Radio Interface

Hybrid

Main Terminal family	DCS-2
Main Terminal size	1.5 mm
Sealed	No
Terminal Size	1.5

Mechanical

Connector mating force	< 60N
-------------------------------	-------

Physical

Color	Blue
Material	PBT
Temperature (Range)	-40°C to +120°C

Terminal 1 Type

Terminal type 1	DCS-2 Female 1.5 mm Terminal
Ways for Terminal Type 1	8
Contact insertion force for Terminal Type 1	< 15N
Retention force (Contact) for Terminal Type 1	> 60N

Environmental

IMDS	Yes
-------------	-----

Other Features

Market	Passenger Vehicles
---------------	--------------------

Type

Part Situation	Female
-----------------------	--------

Disclaimer	Displayed data is for information purposes only. For more information, please contact your local sales office. The supply of some products might be limited to some customers.
-------------------	--