








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—			変更			
			F3	REVISED	ECR-11-010934	11JUL11	TS KB




- △ -Z- 面から2mmの範囲で測定
2. 嵌合相手ハウジング型: 175567, 176243, 917994, 917983
3. 推奨取付ねじ: JIS B1115, B1122 タッピンねじ、なべ2種、呼び径3、長さ6mm以下
(取付けトルク: 0.4N-m以下)
4. 適用製品規格番号: 108-5280, 108-5342
- △ 回路番号: パワー回路 ①~⑩
シグナル回路 ⑪~④②
- △ 適用製品型番のブリフィックス及びIDマークをカラーホットマークにて表示



- △ MUST BE KEPT BETWEEN -Z- AND 2
2. THE MATING PLUG HOUSING PART NUMBER: 175567, 176243, 917994, 917983
3. RECOMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115,B1122
(TIGHTENING TORQUE; 0.4N-m MAX.)
4. APPLICABLE PRODUCT SPEC NUMBER; 108-5280, 108-5342
- △ CIRCUIT NUMBER: POWER CIRCUIT NUMBER ①~⑩
SIGNAL CIRCUIT NUMBER ⑪~④②
- △ INDICATED PREFIX AND ID MARK OF PRODUCT PART NUMBER
BY COLOR HOT MARK

OBSOLETE	9	SELECTIVE-TIN	PRE-TIN	-	-	WHITE	9=176242=1
3	1	TIN-LEAD	SELECTIVE GOLD	1~10	11~42	WHITE	1-176242-1
	2	PRE-TIN X 10		-	11~42	BLUE	2-176242-5
		TIN-LEAD	SELECTIVE GOLD X 32				
	2	PRE-TIN X 10		-	11~42	WHITE	2-176242-1
		TIN-LEAD	SELECTIVE GOLD X 32				
	0	PRE-TIN		-	-	BLUE	176242-5
	0	PRE-TIN		-	-	WHITE	176242-1
MARKING マーキング		SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	COLOR 色	P/N
		CONTACT FINISH コンタクト仕上		 GOLD PLATED CIRCUIT NO. 金めっき回路番号			

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T.SHINOHARA 26JAN07	 TE Connectivity				
DIMENSIONS: 単位: 桁 mm			CHK K.BETSUI 26JAN07					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差			APVD K.BETSUI 26JAN07					
	0 PLC	± -	PRODUCT SPEC 製品規格	NAME 名称	040/070 HYBRID I/O CONNECTOR 42POSITION CAP HOUSING ASSEMBLY			
	1 PLC	± -	SEE NOTE 4					
	2 PLC	± -						
	3 PLC	± -						
	4 PLC	± -	APPLICATION SPEC 取付適用規格					
	ANGLES	± -	-	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO	
MATERIAL 材料	HOUSING: PBT CONTACT: BRASS	FINISH 仕上	SEE TABLE	WEIGHT 20.6 g	A2	00779	C=176242	
CUSTOMER DRAWING				SCALE 尺度		2:1	SHEET 1 of 1	REV F3