

5-Pin *minifast*® Field Wireable Connectors

- Straight Male Connectors
- NEMA 1, 3, 4, 6P
- IEC IP 67 Protection



Drawing	Part Number	Specs	Application	Pinout
BS 41 .. 1.065 [27.0] 3.465 [88.0] APPROX 7/8-16UN	BS 4151-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	
	BS 4151-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	
	BS 4151-0/16	Glass filled nylon PG 16 cable gland, accepts 12-14 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	