

NUMBER
C154979

PANEL RANGE
22 SWG (.028) TO 16 SWG (.064)
[0.71] [1.63] [6.35]

A

1.634
[41.50]1.500
[38.1].140
[3.56].157
[3.99].705 [17.91]
.695 [17.65]1.130 [28.7]
1.120 [28.44].700 [17.78]
.694 [17.62].040 MAX. RAD.
[1.02]

PANEL CUT-OUT RAD.
TO BE ON THIS SIDE IF POSSIBLE

1.000
[25.40]1.773
1.767
[45.03]
[44.88]

PANEL CUT-OUT

SCALE 1:1

1.763
[44.78].595
[15.11].675
[17.14]1.763
[44.78]

VIEW IN DIRECTION
OF ARROW 'A'

M	EB00-0311-00	PB	-	6.00
K	MODIFIED LEAD-IN TO PANEL MOUNTING HOOKS	CB	-	2.35
J	PANEL MOUNTING HOOKS LENGTHENED	CB	-	16.25
H	PANEL MOUNTING HOOKS MODIFIED	CB	-	25.84
G	PANEL CLIP SLOTS RECTIFIED	1P.S.	-	89.172
F	PICTORIAL CHANGE	DC	-	1.112
E	MATE WAS MAKE	DR	-	4.78
D	1.763 DIM. WAS 1.755 (2 PLACES)	KS	-	26.6
C	1000 WAS 1120	264	-	15.916
B	FINISH TABLE ADDED	DR	-	4.78
A	PANEL LATCH MOD. PICT.	262	-	14.78
O	RELEASED FOR PROD.	AKL	-	24.75
LTR	REVISION RECORD	DR	DATE	TOLERANCE EXCEPT AS NOTED
DR	B.C. ROSS	8/4/75	10/1/75	10/1/75
CHK	B.C. ROSS	8/4/75	10/1/75	10/1/75

© AMP of GREAT BRITAIN LTD 1975

MATERIAL AND FINISH
NYLON 6.6

SEE TABLE

WIRE - RANGE - INSULATION

SCALE 4:1

LOC E

NO C

C-154979

HOUSING (PANEL MOUNT)

154979-9	BLACK
-8	GREY
-7	VIOLET
-6	BLUE
-5	GREEN
-4	YELLOW
-3	ORANGE
-2	RED
-1	BROWN
154979-0	NATURAL
PART N°	FINISH

CUSTOMER COPY
REFERENCE ONLYAMP
of Great Britain LtdTERMINAL HOUSE
STANMORE
MIDDLE

PRINT DIST.