



TERMINAL CALL-OUTS MAY
ALSO BE LISTED NUMERICALLY

3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER


SWITCH CHARACTERISTICS

ELECTRICAL RATING	20A 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	650 GMS
RELEASE FORCE MIN.	200 GMS
PRETRAVEL MAX.	.027 [0.7 mm]
OVERTRAVEL MIN.	.005 [0.13 mm]
MOVE. DIFF. MAX.	.008 [0.2 mm]
OPERATING POSITION	.610 TO .641 [15.5 TO 16.3 mm]

NOTES:
RECOMMENDED MOUNTING:
M4 FASTENER WITH 6.00 IN-LB [7.00 KGF-CM] OF TORQUE MAX.

DWN: JED/TLM
APVD: SG
DATE: 20-Jun-05

THIRD ANGLE PROJECTION



THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERRY ELECTRICAL PRODUCTS,
A DIVISION OF THE CHERRY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED

X.XX	X.XXX	ANGLES
± 0.02	± 0.015	± 5

PROJECT / ESK
05-0457A

CHERRY
ELECTRICAL PRODUCTS
NAME / DESCRIPTION

11200 88TH AVENUE
PLEASANT PRAIRIE, WI 53158

SPEC DRAWING

B ITEM NO. GPTBNA01

SCALE: 2:1

SH 1 OF 1

A	12994	20-Jun-05	TLM	SG
REV	ECN NO.	DATE	PREP	APVD