


Dimensions: mm (In.)

**Mechanical Specifications:**

- Mechanical Life: 40,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 2A / 250VAC, 5A / 120 VAC or 28 VDC
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless Steel
- Terminal/Contact: Silver or gold plated
- Switch Support: Brass, Tin plated

Mountain Switch Part No.	Type	Circuit
20126SPDT20	SPDT	On-On
20126SPDT21	SPDT	On-Off-On
20126SPDT22	SPDT	On-(On)
20126SPDT23	SPDT	(On)-Off-(On)

Miniature Toggle Switches

20126SPDT20, 20126SPDT21, 20126SPDT22, 20126SPDT23

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-0020](#)