

YA29LTC78

BURNDY® PRODUCTS

YA29LTC78

YA29LTC78 : COPPER HYLUG-250KCMIL-

7/



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Length (Barrel)		Standard	
Size (Wire)		250 kcmil	
Stud Hole (Size)		7/8 in.	
Stud Hole (Spacing)		One Hole	
Tongue Angle		Straight	
Tongue Width (in)		1.19 in.	
Wire Type		Commercial Stranded Copper	
Strip Length (in)		1-1/8 in.	
Physical			
Element A Index		16	
Approvals / Certifications			
UL Listed		Yes	
CSA Certified		Yes	
Other Features			
UPC		78181055455	
Keyword		ya	