



SYLVANIA**COMPACT
FLUORESCENT LAMP****MINI-LYNX
SPIRO Superior
T2 / 23W****DIMENSIONS (mm)**

Cap Type: E27 -IEC60061-1 sheet -7004-21
Cap Type: B22d -IEC60061-1 sheet -7004-10

ELECTRICAL DATA ¹

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Lamp rated wattage	(W) :	23W		25.3W
Lamp operating voltage (rms)	(V) :	230-240V		
Lamp current	(mA) :	185 mA		
Power Factor	:		0.55	

OPERATING CONDITIONS:

Cap Rim temperature	(°C) :			80
Lamp Ambient Temperature	(°C) :	25	-10	50
Operating Position	:	Unrestricted		
Weight	(g) :	74g		

PERFORMANCE SPECIFICATIONS :

Starting time at 25°C	(s) :			0.3
Warm up Time to 60% stabilized light output	(s) :			40
² Switching Cycles (to 50% Failure)	:		10000	

LAMP LIFE³

Average life (IEC Test Cycle)	(h) :	15000
-------------------------------	-------	-------

PHOTOMETRIC DATA:

	colour no.	Luminous Flux¹ nominal value (lm)	CRI (Class)	Colour Temp. (K)	Energy Efficiency Class	ILCOS Code
Homelight Deluxe	827	1550	1b	2700	A	FBT-23/27/1b-E27-54/127
Homelight Deluxe	827	1550	1b	2700	A	FBT-23/27/1b-B22-54/126

Attention:

Lamps comply with EN 60 968 (Safety Requirements) and EN 60 969 (Performance Requirements) and CE Regulations.

¹Measured according to EN 60 969, at 50 Hz, lamp aged 100h.

²Switching Cycle ON time 60s; OFF time 180s, at rated Voltage.

³Life test according to EN 60 969.



Issued by : R & D Noida
Date : 17.06.2011
Revision Date :

DATA SHEET

Specification No. : TS0014
Supersedes :
Page : 1 of 1

HAVELLS SYLVANIA reserves the right to change data and specification without notice.
Data for guidance only.

SYLVANIA