

Straight Blade Devices

50 Ampere, 125, 250 Volts, 277 Volts AC and 125/250 Volts

2 Pole, 3 Wire Grounding and 3 Pole, 3 Wire Non-Grounding

Single Receptacles and Plugs
50A, 125V
2 Pole, 3 Wire Grounding
Receptacles and Plugs
IP20
 SUITABILITY

50A 125V
 NEMA 5-50R
 UL CSA
 2 HP

50A 125V
 NEMA 5-50P
 UL CSA
 2 HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL9360*
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.2)	HBL9361

Note: *For dimensions, see HBL9308 on page A-37.


50A, 250V
2 Pole, 3 Wire Grounding
Receptacles and Plugs
IP20
 SUITABILITY

50A 250V
 NEMA 6-50R
 UL CSA
 3 HP

50A 250V
 NEMA 6-50P
 UL CSA
 3 HP


Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL9367
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.2)	HBL9368


50A, 277V AC
2 Pole, 3 Wire Grounding
Receptacles and Plugs
IP20
 SUITABILITY

50A 277V AC
 NEMA 7-50R
 UL CSA
 5 HP

50A 277V AC
 NEMA 7-50P
 UL CSA
 5 HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black RTP.	-	HBL9365
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.2)	HBL9379


50A, 125/250V
3 Pole, 3 Wire Non-Grounding
Receptacles, Connector Body and Plugs
IP20
 SUITABILITY

50A 125/250V
 NEMA 10-50P
 UL Listed
 3(2) HP

50A 125/250V
 NEMA 10-50P
 UL Listed
 3(2) HP

Description	Cord Diameter	Catalog Numbers
Receptacle, black phenolic.	-	HBL7962
Receptacle, surface mount aluminum housing.	-	HBL7940
Connector body, Insulgrip, nylon.	.625"-1.218" (15.9-30.9)	HBL7515C
Plug, Insulgrip, nylon.	.625"-1.218" (15.9-30.9)	HBL7513C
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.2)	HBL7977

Note: See page A-46 for accessories.

Representative of surface mount receptacle

