

## CS-S60 CS-S100 Positioning Level Adjuster





### Characteristic

Excellent locomotive function.  
Easy to level adjusting and fixing by operating the handle.

### Application

Machine tools / Physical and chemical devices / Optical devices, etc.



### Parts List

| No. | Part Name       | Material | Finish | Quantity |
|-----|-----------------|----------|--------|----------|
| 1   | Plate           | SPCC     | UC     | 1        |
| 2   | Adjuster Handle | PA       | Black  | 1        |
| 3   | Frame           | SPCC     | UC     | 1        |
| 4   | Main Shaft      | SS400    |        | 1        |
| 5   | Roller Shaft    | PA       | Black  | 1        |
| 6   | Foot            | NBR      |        | 1        |
| 7   | E-Ring          | S        | UC     | 2        |

※No. 7 E-Ring is not included in CS-S60.

| Model No. | A    | B   | C  | D   | E     | F  | G    | H  | J  | K   | L  | Allowable Vertical Compressive Load kN (kgf) | Net Weight (g) | Code No. |
|-----------|------|-----|----|-----|-------|----|------|----|----|-----|----|----------------------------------------------|----------------|----------|
| CS-S60    | φ115 | 85  | 68 | 86  | t 4.5 | 36 | 12   | 7  | 25 | φ50 | 25 | 589 (60)                                     | 937.5          | 6067     |
| CS-S100   | φ140 | 110 | 90 | 116 | t 6   | 64 | 14.8 | 17 | 36 | φ70 | 30 | 981 (100)                                    | 2219           | 6068     |

## CS-W30 CS-W60/CS-W100 Positioning Level Adjuster





### Characteristic

Combined and downside caster mechanism, vibration absorption and adjusting.  
Double wheel smooth rotating caster.  
Easy to adjust level and fixing by operating the handle.

### Application

Office automation appliances / Office utilities / Furniture, etc.



### Parts List

| No. | Part Name        | Material | Finish | Quantity |
|-----|------------------|----------|--------|----------|
| 1   | Plate            | SPCC     | Uc     | 1        |
| 2   | Adjuster Handle  | PA       | Ivory  | 1        |
| 3   | Roller Shaft     |          | Brown  | 2        |
| 4   | Frame            | ADC      | —      | 1        |
| 5   | Foot             | PA       | Brown  | 1        |
| 6   | Isolation Rubber | NBR      | Black  | 1        |

### Specification

| Model No. | A   | B   | C  | D    | E   | F    | G  | H  | J   | K    | L   | M    | N      | Allowable Vertical Compressive Load kN (kgf) | Net Weight (g) | Code No. |
|-----------|-----|-----|----|------|-----|------|----|----|-----|------|-----|------|--------|----------------------------------------------|----------------|----------|
| CS-W30    | 70  | 45  | 32 | φ6.6 | 70  | t2.3 | 7  | 10 | 75  | 17.5 | φ45 | 30.4 | (54.4) | 294 (30)                                     | 151.5          | 6062     |
| CS-W60    | 100 | 70  | 50 | φ7   | 85  | t3.2 | 10 | 12 | 102 | 22   | φ60 | 40   | (70)   | 589 (60)                                     | 357.5          | 6063     |
| CS-W100   | 140 | 100 | 72 | φ11  | 120 | t4.5 | 12 | 17 | 138 | 28   | φ80 | 50.5 | (94.5) | 981 (100)                                    | 872            | 6064     |