


1

2


3

4


5



MATING PART
3230-XX-0101-00




MATING PART
3230-XX-0102-00



Specifications:
Current rating:1.0A
Voltage rating:50V AC,DC
Contact resistance:20m ohm Max
Insulation resistance:1,000M ohm Min
Withstanding voltage:500V AC/minute
Operating Temperature:-40°C ~ +105°C

Materials:
Insulator:Nylon6T (UL94V-0)
Standard Color:Black
Contact:Brass
Plating:Gold Plated Over Nickel

Circuits	DIM		Circuits	DIM	
	A	B		A	B
10	5.08	20.70	40	24.13	39.75
16	8.89	24.51	44	26.67	42.29
20	11.43	27.05	50	30.48	46.10
26	15.24	30.86	60	36.83	52.45
30	17.78	33.40	68	41.91	57.53
34	20.32	35.94			



RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
				CHECKED:	UNIT: MM	DESCRIPTION: 1.27mm Shrouded Header R/A Type	SIZE A4
					SCALE:1:1		
	05-FEB-2020			APPROVAL:	SHEET: 1 / 1	PART NO: 3210-XX-002-12-00	
REV	DATE	FILE	BY		PROJECTION: 		