



LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				V	REV PER 0G3A-0561-01	090CT02	JR/MS



1 CIRCULAR MIL AREA RANGE: 52,600-83,700 CM
2 TIN PL 0.00381 [.000150] MIN THK PER MIL-T-10727



326799		
PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH 2		
DR 02/28/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
CHK 18JAN95 MS FEHER		
APPD 18JAN95 WJ VOCKROTH	NAME TERMINAL, AMPPOWER™ WIRE SIZE: 2 AWG	
APPD 18JAN95 TL SHUTTER		
PRODUCT SPEC 108-30200	SIZE C CAGE CODE 00779 DRAWING NO 326799	
APPLICATION SPEC -		
WEIGHT .038 LB	SCALE 2:1	SHEET 1 OF 1