


70-402-1 Socket/10 Amp Rating, 300 Volts



Printed Circuit
Board Mounting



BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED

Standard Part Number

Description

70-402-1

8 Pin, Printed Circuit Terminals

General Specifications

Characteristics	Units	Value
Number of Terminals		8
Electrical Rating		
Nominal Voltage Rating	Volts	300
Nominal Current Rating	Amps	10
Dielectric Strength		
Output to Input Terminals	V rms	1500
Output to Adjacent Output Terminals	V rms	1500
Temperature		
Operating Range:	°C	- 40 to + 80
Storage Range:	°C	- 40 to+ 105
Construction		
Internal Metal Tracks		Copper Alloy, Zinc Plated
Terminals		Copper Alloy, Zinc Plated
Miscellaneous		
Socket Mounting:		Printed Circuit
Connection Method		Solder
Flamability Rating	Class	94V-0
Body Color		Light Gray
Product Certification		UL, CSA
Conformance		CE, RoHS
Weight	grams	6.5

Optional Mating Accessories



782 Relays



16-1324



16-1342

Standard Part Number	Description	Catalog Location
782	Relay	Section 1 p.12-13
16-1324	Metal Hold-Down Clip, Front to Back, 782 Plain Cover Relay Only	Section 3 p.8-11
16-1342	Metal Hold-Down Clip, Side Mount	Section 3 p.8-11

