





A


B

C

D



PC board drilling dimensions(after plating)  
(thickness ≤ 3.20±0.30mm)



## TIN LEAD PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER  | PART NUMBER  |
|-------|--------|--------|--------|--------|--------|--------------|--------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P91C4PA00 | D09P91C6PA00 |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P91C4PA00 | D15P91C6PA00 |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P91C4PA00 | D25P91C6PA00 |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P91C4PA00 | D37P91C6PA00 |
|       |        |        |        |        |        | gold flash   | 0.76µ gold   |

## LEAD FREE PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER    | PART NUMBER    |
|-------|--------|--------|--------|--------|--------|----------------|----------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P91C4PA00LF | D09P91C6PA00LF |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P91C4PA00LF | D15P91C6PA00LF |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P91C4PA00LF | D25P91C6PA00LF |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P91C4PA00LF | D37P91C6PA00LF |
|       |        |        |        |        |        | gold flash     | 0.76µ gold     |

## GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

|                                                                                       |         |            |                                                                  |        |                                   |       |                                                                                                     |            |                                                                                             |  |
|---------------------------------------------------------------------------------------|---------|------------|------------------------------------------------------------------|--------|-----------------------------------|-------|-----------------------------------------------------------------------------------------------------|------------|---------------------------------------------------------------------------------------------|--|
| www.fciconnect.com                                                                    |         |            | surface<br>ISO 1302                                              |        | tolerance std<br>ISO 406 ISO 1101 |       | projection<br> |            | mm<br> |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED                                                 |         |            |                                                                  |        |                                   |       |                                                                                                     |            |                                                                                             |  |
| Dr                                                                                    | JOUBERT | 1995/08/11 | ANGULAR                                                          | LINEAR | 0.X                               | ±0.1  | size<br>A3                                                                                          | Scale<br>2 |                                                                                             |  |
| Eng                                                                                   | PESSON  | 1995/08/11 |                                                                  |        | 0.XX                              | ±0.1  |                                                                                                     |            |                                                                                             |  |
| Chr                                                                                   | LEGARE  | 1995/08/11 |                                                                  |        | 0.XX' ±2°                         | 0.XXX |                                                                                                     |            |                                                                                             |  |
| Appr                                                                                  | LEGARE  | 1995/08/11 | Product family                                                   |        |                                   |       | D-SUB                                                                                               | Spec ref - |                                                                                             |  |
|  |         |            | title<br>MALE CONNECTOR DELTA D STD EUROPE<br>straight press-fit |        |                                   |       | dwg no<br>C01-8646-0109                                                                             |            | Rev.<br>K                                                                                   |  |
| catalog no                                                                            |         |            | -                                                                |        |                                   |       | CUSTOMER                                                                                            |            | sheet 1 of 1                                                                                |  |

| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| G   | -         | -   | 1996/07/16 |
| H   | LS05-004  | MPE | 2005/02/07 |
| J   | LS06-0095 | LGO | 2006-06-17 |
| K   | LS06-0140 | LGO | 2006-09-22 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |

A

B

C

D