

General Information

Extended Product Type:	M4/6
Product ID:	1SNA115116R0700
EAN:	3472591151169
Catalog Description:	M4/6
Long Description:	M4/6 Screw Clamp Terminal Blocks Feed-through

Categories

Products	»	Low Voltage Products and Systems	»	Connection Devices	»	Terminal Blocks	»	Screw Clamp Terminal Blocks
----------	---	----------------------------------	---	--------------------	---	-----------------	---	-----------------------------

Ordering

EAN:	3472591151169
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	8,7 g
---------------------	-------

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	0.44 kg
Package Level 1 EAN:	3472591151169
Package Level 2 Units:	2000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	18.1 kg
Product Packing Type:	Box

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Additional Information

Color:	grey
Connection Type:	Screw clamp
Dielectric Test Voltage:	3500 V
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Pollution Degree:	3
Product Main Type:	M4/6
Product Name:	Terminal block
Rated Impulse Withstand Voltage (U _{imp}):	8 kV
Recommended Screw Driver:	4 mm
Spacing:	6 mm
Sub-Function:	2 connections
Tightening Torques:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
Wire Stripping Length:	9.5 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1000
GOST Certificate:	1SND161005A1103

Classifications

E-number:	2925506
Object Classification Code:	X

