

APPLICATOR PARTS LIST

TYPE

SIDEWISE PIN RECEIPT

AMP INCORPORATED
HARRISBURG, PENNA.

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS
1	■ WIRE CRIMPER	1	4539323	42	■ SHEAR PLATE-LEFT	1	811855-1	TO APPLY TERMINAL			GROUP I
2	■ INS. CRIMPER	1	2465264-2	43	■ SHEAR BLOCK RIGHT	1	386372	CRIMP HEIGHT			.010 X .035
3	■ ANVIL	1	811225-4	44	■ FLOATING SHEAR	1	465406	WIRE SIZE	GROUP I	GROUP II	60354
4	ANVIL SPACER	1	810070-5	45	RETAINING PLATE FRT.	1	811714-3		60354	60804	
5	■ SHEAR BLADE			46	RETAINING PLATE REAR	1	386370	28	.025		
6	■ REAR SHEAR PLATE			47	■ SPRING SHEAR RETURN	1	374322	26	.027	.026	
7	SPACER REAR ANVIL	1	452621-1	48	SHEAR DEPRESSOR	1	811101-2	24		.029	
8	■ FRONT SHEAR PLATE			49	KEY SHEAR RET.	1	386358	22		.032	
9	REAR ANVIL SPACER PLT.			50	GUARD MOUNT	1	811306-1	CRIMP	SIZE	TYPE	FEED
10	FRONT ANVIL SPACER PLT.			51	HOLDER, PUNCH	1	810498-3	WIRE	.055	F	
11	TOOL SPACER	1	4704937	52	PUNCH ASSY	1	810738-1	INSUL.	.070	O	.255
12	CRIMP SPACER	1	375548	53				SLEEVED			
13	FRONT STRIP GUIDE	1	810971-1	54	REAR STRIP GUIDE BODY	1	811527-3	INSULATION RANGE	WIRE RANGE		
14	REAR STRIP GUIDE	1	465440-4	55				.035 - .045	28 - 26	60354	
				56				.035 - .065	26 - 22	60804	GROUP II
15	RAM	1	471912	57				EXPLODED VIEW			.010 X .135
16	TOOL HOLDER			58				A-6002-13	A-6002-13		60804
17	ADJ. CRIMP MOUNT			59				REMARKS:			
18	ADJ. BLOCK	1	811102-1	60	SCREW, SOC. HD CAP	3	811651-3	▲ USE WITH ITEM 22 IS			
19	APPLICATOR MOUNT ASSY.			61							
20	BASE PLATE	1	465100	62							
21	BASE BLOCK	1	465101	63							
22	STRIP GUIDE PLATE	1	465414-1	64	1" AIR FEED ASSY.	1	690021				
23	ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999				
24	WIRE STOP GUIDE	1	811787-1		MISCELLANEOUS						
25	STRIPPER - WIRE STOP	1	386361-1	66							
26	STRIPPER MOUNT	1	386362	67	LUBRICATOR ASSY	1	465184-2				
27	RETAINER PLATE	1	389078	68	OIL, SYNTHETIC	1	22014-1				
28	STRIPPER MOUNT BRACKET	1	387715-1	69							
29	STRIPPER BUSHING	1	389049-1	70							
30	STOCK DRAG	1	386955	71							
31	STOCK DRAG HANDLE			72							
32	STOCK DRAG STUD	1	374900		REV. REVISION RECORD	DATE	BY	ECN			
33	STOCK DRAG SPRING	1	370572		REDRAWN W/CHANGES	1-4-73	RS	1-9-73			
34	STOCK DRAG ADJ. NUT	1	21022-3		ITEM 45 WAS -2, ADD ITEM 60804						
35	FEED FINGER HOLDER	1	386942		M1 REV. PER ECN	4-4-73	RS	4-9-73			
36	FEED FINGER	1	386941		M1 CH 60804 #26 W/ 028, 033	5-24-73	RS	1-9-75			
37	FEED FINGER TIP	1	387251		M1 REV. PER ECN	7-23-73	RS	6-9-73			
38	FEED FINGER GUIDE	1	689915-2		P REV. PER ECN	3-1-75	RS	1-10-73			
39	BASE CASTING	1	570238		R REV. PER ECN	5-19-76	RS	6-1-76			
40	GUARD	1	811303-1		R1 INACTIVE FPC	2-24-77	RS	6-1-76			
41	BRACKET GUARD	1	811304-1								

— INACTIVE —
FOR REPLACEMENT ONLY

■ DENOTES WEARING PARTS
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON
AMP-O-ELECTRIC 1-471273-2
AIR FEED

SERIAL NO. DATE SHIPPED

CUSTOMER NAME AND ADDRESS

APPLICATOR REV. NUMBER 565739-1

SHEET 1 OF 1

FOR HARDWARE
SEE 687511-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[565739-1](#)