






SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PA00	D09S91C6PA00
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PA00	D15S91C6PA00
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PA00	D25S91C6PA00
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PA00	D37S91C6PA00
						gold flash	0.76 μ gold

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PA00LF	D09S91C6PA00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PA00LF	D15S91C6PA00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PA00LF	D25S91C6PA00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PA00LF	D37S91C6PA00LF
						gold flash	0.76μ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:	
SEE DRAWING C01-8646-0001	

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS		OTHERWISE SPECIFIED						
Dr	JOUBERT	1995/08/11	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	PESSON	1995/08/11			0.XX	±0.1					
Chr	LEGARE	1995/08/11			0.XX' ±2'	0.XXX		±0.1			
Appr	LEGARE	1995/08/11	Product family				D-SUB	Spec ref -			
			title FEMALE CONNECTOR DELTA D STD EUROPE straight press-fit				dwg no C01-8646-0127	Rev. J			
catalog no											
							CUSTOMER		sheet 1 of 1		

rev	ecn no	dr	date
F	-	-	1996/07/1
G	LS05-004	MPE	2005/02/07
H	LS06-0095	LGO	2006/06/19
J	LS06-0140	LGO	2006/09/22
-	-	-	-
-	-	-	-
-	-	-	-