






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code				surface		tolerance	projection	product family			
NOTES 1 & 2				ISO 1302		ISO 406		CARD CONN			
						ISO 1101					
ltr	ecr	no	dr	date	tolerances unless otherwise specified			title			
D	V23244	MRC	10/01/92		angles	linear		2X.100/2.54 VERT. CARD CONN.			
E	V70794	LSS	11/7/97					.050/1.27 LEG 15 Au			
F	M05-0216	ERE	10/11/05	0'±2'				scale 4:1			
G	M06-0210	MHT	6/03/06	dr	L.SANDERS	11/7/97		dwg no			
				enr	H.SUNDY	11/7/97		sheet 1 of 3 size			
				chr	H.SUNDY	11/7/97		68428 A3			
				appd	H.SUNDY	11/7/97		type Product Customer Drawing			
sheet	revision	G	G								
index	sheet	1	2	3							

form: A3


PDM: Rev:G

STATUS:Released

Printed: Dec 12, 2008

PRODUCT NUMBER

SEE TABLE

RECOMMENDED HOLE PATTERN
SCALE 5/1

NOTES:

- ① HOUSING MAT'L: FILLED POLYESTER,
FLAME RETARDANT PER UL 94V-0.
COLOR : BLACK.
- ② TERMINAL MATERIAL.
BODY: BRASS
GOLD FLASH, WITH 15u"/0.38u Au OVER
50u"/1.27u Ni IN CONTACT AREA.
SPRING MATERIAL: BeCu ALLOY HEAT TREATED.
SPRING PLATING: GOLD FLASH.
3. MARKING: "FCI PART NUMBER AND DATE CODE LEGIBLE
ON TUBE LABEL.
4. APPLICATION INFORMATION:
A. RECOMMENDED MOUNTING HOLE PATTERN
IS SHOWN IN FIG. "A"
B. ALL MATING PINS TO BE .025/.64 SQ
ON TRUE CENTER OF GIVEN TERMINAL
SPACING WITHIN .015/.38 DIAMETER.
C. SUGGESTED MATING PIN LENGTH .210/5.33 +
.040/1.02 - .060/1.52.
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD
FREE OPTION.
- ⑥ THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED
OR VAPOR PHASE SOLDER PROCESS.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CARD CONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
G					angles linear .XX±.01/.X±.3		2X.100/2.54 VERT. CARD CONN.
					0'±2' .XXX±.0.005/.XX±.13		.050/1.27 LEG 15 Au
					.XXXX±.0020/.XXX±.051		scale 4:1
			dr	L.SANDERS	11/7/97		dwg no
			enr	H.SUNDY	11/7/97		sheet 2 of 3
			chr	H.SUNDY	11/7/97		size A3
			appd	H.SUNDY	11/7/97		type Product Customer Drawing
sheet index	revision sheet						



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM A	DIM B MAX	LEAD FREE OPTION
68428-001	UNASSIGNED			NOTE 5,6
-002	2 X 2	.100/2.54	.200/5.08	
-003	2 X 3	.200/5.08	.300/7.62	
-004	2 X 4	.300/7.62	.400/10.16	
-005	2 X 5	.400/10.16	.500/12.70	
-006	2 X 6	.500/12.70	.600/15.24	
-007	2 X 7	.600/15.24	.700/17.78	
-008	2 X 8	.700/17.78	.800/20.32	
-009	2 X 9	.800/20.32	.900/22.86	
-010	2 X 10	.900/22.86	1.000/25.40	
-011	2 X 11	1.000/25.40	1.100/27.94	
-012	2 X 12	1.100/27.94	1.200/30.48	
-013	2 X 13	1.200/30.48	1.300/33.02	
-014	2 X 14	1.300/33.02	1.400/35.56	
-015	2 X 15	1.400/35.56	1.500/38.10	
-016	2 X 16	1.500/38.10	1.600/40.64	
-017	2 X 17	1.600/40.64	1.700/43.18	
-018	2 X 18	1.700/43.18	1.800/45.72	
-019	2 X 19	1.800/45.72	1.900/48.26	
-020	2 X 20	1.900/48.26	2.000/50.08	
-021	2 X 21	2.000/50.08	2.100/53.34	
-022	2 X 22	2.100/53.34	2.200/55.88	
-023	2 X 23	2.200/55.88	2.300/58.42	
-024	2 X 24	2.300/58.42	2.400/60.96	
68428-025	2 X 25	2.400/60.96	2.500/63.50	NOTE 5,6

PRODUCT NO	NO. OF POS.	DIM A	DIM B MAX	LEAD FREE OPTION
68428-026	2 X 26	2.500/63.50	2.600/66.04	NOTE 5,6
-027	2 X 27	2.600/66.04	2.700/68.58	
-028	2 X 28	2.700/68.58	2.800/71.12	
-029	2 X 29	2.800/71.12	2.900/73.66	
-030	2 X 30	2.900/73.66	3.000/76.20	
-031	2 X 31	3.000/76.20	3.100/78.74	
-032	2 X 32	3.100/78.74	3.200/81.28	
-033	2 X 33	3.200/81.28	3.300/83.82	
-034	2 X 34	3.300/83.82	3.400/86.36	
-035	2 X 35	3.400/86.36	3.500/88.90	
68428-036	2 X 36	3.500/88.90	3.600/91.44	NOTE 5,6

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1 	title
G				angles	linear .XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		2X.100/2.54 VERT. CARD CONN. .050/1.27 LEG 15 Au
				0'±2'			
		dr	L.SANDERS	11/7/97			dwg no
		enr	H.SUNDY	11/7/97			sheet 3 of 3 size
		chr	H.SUNDY	11/7/97			68428 A3
		appd	H.SUNDY	11/7/97			type Product Customer Drawing
sheet index	revision sheet						

form: A3