





|           |            |          |                                             |           |        |
|-----------|------------|----------|---------------------------------------------|-----------|--------|
| PART NAME | ECONOBOXES | PART No. | CU-5470 TO CU-5479 & CU-5470-B TO CU-5479-B | REV. DATE | 5-8-08 |
|-----------|------------|----------|---------------------------------------------|-----------|--------|



MATERIAL:  
ALUMINUM ALLOY #ADC-12  
FINISH:  
NATURAL (NO SUFFIX)  
SMOOTH BLACK (SUFFIX -B)

ALL INTERNAL FILLETS 0.062 RADIUS  
ALL INTERNAL ROUNDS 0.125 RADIUS  
ALL EXTERNAL ROUNDS 0.125 RADIUS  
ALL BOXES ASSEMBLED WITH #6-32 FLAT HD. SCREWS



\* ASSEMBLED HEIGHT

| PART NO. | PART NO.  | A     | B     | * C   | D     | E     | F     | G     | H     | J     | K     | L     | M     | N     | P     |
|----------|-----------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| CU-5470  | CU-5470-B | 2.000 | 2.000 | 1.250 | 1.094 | 1.625 | 1.625 | ---   | ---   | 0.065 | 0.065 | 0.188 | 2.468 | 1.625 | 2.486 |
| CU-5471  | CU-5471-B | 4.330 | 3.250 | 1.750 | 1.594 | 3.955 | 2.875 | ---   | ---   | 0.094 | 0.078 | 0.188 | 3.718 | 3.954 | 3.736 |
| CU-5472  | CU-5472-B | 4.750 | 3.150 | 2.330 | 2.174 | 4.375 | 2.775 | ---   | ---   | 0.094 | 0.078 | 0.188 | 3.618 | 4.374 | 3.636 |
| CU-5473  | CU-5473-B | 4.688 | 3.688 | 1.340 | 1.184 | 4.313 | 3.313 | ---   | ---   | 0.094 | 0.078 | 0.188 | 4.156 | 4.312 | 4.174 |
| CU-5474  | CU-5474-B | 4.750 | 4.750 | 2.330 | 2.174 | 4.375 | 4.375 | ---   | ---   | 0.094 | 0.078 | 0.188 | 5.218 | 4.375 | 5.236 |
| CU-5475  | CU-5475-B | 4.750 | 4.750 | 3.750 | 3.594 | 4.375 | 4.375 | ---   | ---   | 0.094 | 0.078 | 0.188 | 5.218 | 4.375 | 5.236 |
| CU-5476  | CU-5476-B | 6.000 | 3.250 | 2.000 | 1.844 | 5.610 | 2.860 | 2.805 | ---   | 0.094 | 0.078 | 0.195 | 3.718 | 5.604 | 3.736 |
| CU-5477  | CU-5477-B | 7.390 | 4.703 | 1.500 | 1.344 | 7.000 | 4.313 | 3.500 | ---   | 0.094 | 0.078 | 0.195 | 5.172 | 7.000 | 5.190 |
| CU-5478  | CU-5478-B | 7.500 | 7.500 | 2.620 | 2.464 | 7.110 | 7.110 | 3.555 | 3.555 | 0.094 | 0.078 | 0.195 | 7.968 | 7.110 | 7.986 |
| CU-5479  | CU-5479-B | 4.375 | 2.375 | 2.136 | 1.980 | 4.000 | 2.000 | ---   | ---   | 0.065 | 0.078 | 0.188 | 2.844 | 4.000 | 2.862 |