

## HTAT-12/3-0-STK Product Details

[Share](#)[Print](#)[Email](#)

HTAT-12/3-0-STK

TE Internal Number: 7465232006



### Heat Shrink Tubing



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Heat Shrinkable Tubing
- Product Name = HTAT
- Product Source = U.K., U.S.
- Semiflexible
- Thin Wall Style

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Crosslinked Polyolefin
- Color = Black

#### Electrical Characteristics:

- Product Source = U.K., U.S.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 12.00 [0.472]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 3.00 [0.118]
- Product Use = Connector-to-Cable Transitions
- [Cut Length \(mm \[in\]\)](#) = 1220.00 [48.068]

#### Body Related Features:

- [Product Name](#) = HTAT
- Pliancy = Semiflexible
- [Wall Style](#) = Thin
- [Wall Type](#) = Dual
- [Lining Type](#) = Adhesive
- [Shrink Ratio](#) = 4:1
- Fluid Resistance = Moisture, Splash Protection
- Fluid Type = Brake Fluid, Chemicals/Solvents, Hydraulic Fluid, Lubricating Oil, Water
- Resistant To = Fluids, Mechanical Damage, Strain
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 1.40 [0.0551]

#### Housing Related Features:

- Material Systems = No
- Flammability Rating Type = Flame-Retardant

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- UL Rating = None
- CSA Certified = No
- Approved Standards = None
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Full Recovery Temperature (°C) = 110
- Shrink Temperature, Min. (°C) = 80
- [Operating Temperature \(°C\)](#) = -55 - +125
- High Temperature Compatible = Yes

#### Operation/Application:

- Application = Sealing
- Emission Free = No

#### Packaging Related Features:

- Packaging Method = Stick

#### Other:

- Brand = Raychem

### Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

### Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

### Customer Support

[Email or Chat with Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)

### Sign up for our eNewsletter



### Follow Us On:



Visit Us On:

