




Electrical Characteristics
Nominal Impedance: 50 ohms
Frequency Range: DC to 2.5 GHz
Operating Voltage (rms): 335 V maximum at sea level

Mechanical Characteristics
Mating Cycles: 500 cycles minimum

Environmental Characteristics
Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Dielectric	POM
3	Contact	Brass, gold plated

First Issue	SN	1	02 Oct 02
DESCRIPTION OF REVISION	APPVD	ISS	DATE

 Cinch Connectivity Solutions 7-13 Russell Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515 Fax: +44 (0) 1245 358938	SCALE: Not To Scale	DRAWN BY:	S Nash	TITLE: BNC Jack to Mini UHF Plug	PART NUMBER: VA301
	DIMENSIONS: mm	CHECKED BY:	P Couzens		
	TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		
		DATE:	02 Oct 02		PAGE: 1 of 1