





D-Sub Connectors

156-1209, 156-1225, 156-1309, 156-1325,
156-1215, 156-1237, 156-1315, 156-1337

KOBICONN

D-Sub Connectors

156-1209, 156-1225, 156-1309, 156-1325, 156-1215, 156-1237, 156-1315, 156-1337



Mouser Stock Number				Dimension (In.)				
Plugs	A	Receptacles	A	B	C	D	E	
156-1209	.643	156-1309	.666	.984	1.213	.759	.235	
156-1215	.971	156-1315	.994	1.312	1.541	1.083	.235	
156-1225	1.511	156-1325	1.534	1.852	2.088	1.625	.230	
156-1237	2.159	156-1337	2.182	2.500	2.729	2.272	.230	

Material Specifications

Shell:	zinc plated steel
Contacts:	stamped 1.1~1.5 microns gold plated nickel
Insulator:	PBT & glass fibre reinforced

Electrical Specifications

Current Rating:	5A
Dielectric Strength:	1000V for 1 minute
Insulator Resistance	1000MΩ min. @ 500VDC
Temperature:	-55°C ~ +105°C
Maximum Wire Gauge:	24 AWG

Date Last Revised: 10-17-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300102

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[156-1225](#) [156-1315](#) [156-1215](#) [156-1325](#) [156-1309](#) [156-1209](#)