


MIL-C-26482
MIL-C-83723
Series I Bayonet
650DS001 B 16

Basic Part No.

Finish (Table IV)

Shell Size


TABLE III: DIMENSIONS

Shell Size	E Dia	F Max	G	H Dia ±.010 (0.3)	J	K
08	.471 (12.0)	.828 (21.0)	.594 (15.1)	.120 (3.0)	.478 (12.1)	.062 (1.6)
10	.588 (14.9)	.954 (24.2)	.719 (18.3)	.120 (3.0)	.478 (12.1)	.062 (1.6)
12	.748 (19.0)	1.047 (26.6)	.812 (20.6)	.120 (3.0)	.478 (12.1)	.062 (1.6)
14	.873 (22.2)	1.141 (29.0)	.906 (23.0)	.120 (3.0)	.478 (12.1)	.062 (1.6)
16	.998 (25.3)	1.234 (31.3)	.969 (24.6)	.120 (3.0)	.478 (12.1)	.062 (1.6)
18	1.123 (28.5)	1.328 (33.7)	1.062 (27.0)	.120 (3.0)	.478 (12.1)	.062 (1.6)
20	1.248 (31.7)	1.453 (36.9)	1.156 (29.4)	.120 (3.0)	.572 (14.5)	.094 (2.4)
22	1.373 (34.9)	1.578 (40.1)	1.250 (31.8)	.120 (3.0)	.572 (14.5)	.094 (2.4)
24	1.498 (38.0)	1.703 (43.3)	1.375 (34.9)	.147 (3.7)	.605 (15.4)	.094 (2.4)

TABLE IV: STANDARD FINISHES

Finish Symbol	Finish
B	Cadmium Olive Drab
C	Anodize, Black
M	Electroless nickel
NF	500 hr Cadmium Olive Drab

1. For complete dimensions see Military Standard MS3115.
2. Metric dimensions (mm) are indicated in parentheses.