

 Direct Link

 Cross reference

 RoHS/LF P/N Search

 Customer drawing search

 3D model search

 Application tooling

 Services

 Contact us

 Distributor list

 Price request

 Order samples

 Documentation

 Free search

 Search by category

Start > Search=59453-081110EALF* > 59453-081110EALF

 59453-081110EALF - FPC/FFC : SFVL Series, 8 Pos, Lower Side Contact, Side Entry Surface Mount ZIF Connector, 0.5 mm (0.02 in.), All Gold Plating

ACTIVE

Electronics division

RoHS compatible

 Customer Drawing

Specifications Download document

 Assistant

 Add to Favorites

 Email Datasheet

 Print Datasheet

FCI Brings You More

 Contact our sales/technical support

 Sample request

 Price request

 Check distributor stock

General Electrical Mechanical Physical Approvals / Certifications Other Features

General	
Cable Lock	Yes
Contact location	Lower
Number of contacts	8
Orientation	Right Angle
Product Series	SFVL
Electrical	
Withstanding Voltage	200V AC for 1 minute
Current rating	0.4A AC/DC
Resistance (Contact)	30 milli ohms max.
Resistance (Insulation)	100 M-ohms min.
Voltage rating	50V AC/DC
Mechanical	
Durability (Mating cycles)	10 Cycles
Physical	
Material (Contact)	Copper Alloy, Gold Plated
Material (Housing)	Glass Reinforced LCP, UL94 V-0
Material (Slider)	Glass Reinforced PPS, UL94 V-0
Temperature (Range)	-40°C to +85° C
Approvals / Certifications	
Damp Heat per JIS C 0022	Difference from initial value 20 milli ohms max.
Salt Spray per JIS C 0023	Difference from initial value 20 milli ohms max.
Temperature Cycling per JIS C 0025	Difference from initial value 20 milli ohms max.
Vibration per JIS C 0040	No discontinuity > 1 µ second
Other Features	
Packaging (Type)	Embossed Tape on Reel