




HAMMOND
MANUFACTURING®

www.hammondmfg.com

166J12B

Power Transformer - Low Voltage/ Filament
Economical Single Primary - Open Style Chassis Mount



Features

- Economical single primary 115 VAC, 60 Hz. (or 117 50/60 Hz. see table below)
- Open style, channel bracket, chassis mount.
- Minimum 6" long leads.
- Dual bobbin design - no electrostatic shield required.
- Class B insulation (130 degrees, C) for extra protection - **UL listed** as a Class A (105 degree, C) design
- Hi-Pot test of 2,000V RMS.
- **CSA certified.**

| Overall Dimensions (in. / mm) | |
|-------------------------------|----------------|
| A | 3.25 / 82.6 |
| B | 1.75 / 44.5 |
| C | 2 / 50.8 |
| Hole to Hole Mounting Dims | |
| D | 2.81 / 71.4 |
| E | / |
| Mounting Hole Sizes | |
| Width-wise | 0.187 / 4.7 |
| Depth-wise | / |
| Electrical | |
| Size (VA) | 12.6 |
| Primary | 117V 50/60 Hz. |
| Secondary VAC | 12.6 C.T. |
| Secondary Amps | 1 |

Schematic

