






MATERIALS AND FINISH:

SHELL: STEEL MATERIAL, NICKEL FINISH
INSULATOR: PA6T = 260°C, UL 94V-0 RATED, BLACK
CONTACT MATERIAL: BRASS
CONTACT FINISH: FULL GOLD FLASH

ELECTRICAL:

CONTACT CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 30 Milliohms Max.
DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
INSULATION RESISTANCE: 5,000 Megohms Min.
TEMPERATURE RATING: -55° ~ +105° C

180-MYY-21YRYYY

SERIES _____
MACHINED CONTACTS _____
POSITION _____
15
26
44
62
GENDER _____
2 = FEMALE
TERMINATION _____
1 = VERTICAL DIP
SHELL PLATING _____
3 = NICKEL
RoHS (HIGH TEMP.) 260° PROCESS _____
HARDWARE _____
00 = $\text{Ø} 0.120"$ HOLE
01 = 0.098" 4-40 INSERT, BOARD SIDE
02 = 0.250" 4-40 INSERT, BOARD SIDE
03 = 0.250" 4-40 INSERT, MATING SIDE
05 = 0.224" BOARD LOCK, BOARD SIDE
91 = 0.224" BOARD LOCK, BOARD SIDE
0.189" SCREW LOCK, MATING SIDE
CONTACT PLATING _____
1 = GOLD FLASH, ENTIRE CONTACT
2 = 30u" GOLD, ENTIRE CONTACT

DIMENSIONS (IN.)						
No. OF PINS	A	B	C	D	E	F
15	0.643	0.984	1.213	0.759	0.010	0.090
25	0.971	1.312	1.541	1.083	0.020	0.090
44	1.511	1.852	2.088	1.625	0.020	0.090
62	2.159	2.500	2.729	2.272	0.023	0.094

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-16-07	
		CHECKED:		DATE:	
		SCALE: 1 : 1		SHEET 1 OF 3	
		DWG NO. 180-MYY-21YRYYY			

RoHS COMPLIANT


TOLERANCE:
ALL DIMENSIONS ARE ±0.010

ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS

05X 0.224" BOARD SIDE - CN10




91X 0.224" BOARD SIDE
0.189 MATING SIDE
CN10/SFSO4404




NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE


01X 0.098" (BOARD SIDE) - CN1



02X 0.250" (BOARD SIDE) - CN2




03X..... 0.250" (MATING SIDE) - CN8




DO NOT SCALE FROM DRAWING

RoHS COMPLIANT


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 02-12-08	
		CHECKED:		DATE:	
	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE:	SHEET 2	OF 3	REV 4
		DWG NO. 180-MYY-21YRYYY			




15 POSITION



26 POSITION



44 POSITION



62 POSITION

* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-16-07		
			CHECKED:		DATE:		
			SCALE: 1 : 1		SHEET 3 OF 3		REV 4
			DWG NO. 180-MYY-21YRYYY				