



Specifications:
 Current Rating:1.0A AC/DC
 Voltage Rating:30V AC/DC
 Contact Resistance:20m ohm. Max.
 Insulation Resistance:1000M ohm. Min.
 Withstanding Voltage:500V AC For One Minute
 Operating Temperature Rating:-40°C ~ + 105°C
 Materials and Finish
 Insulator:PBT (UL94V-0)
 Insulator Color:Black
 Contact:Copper Alloy
 Plated:Selective Gold Plated

TOTAL NO. OF PINS	DIM		
	A±0.30	B±0.15	C±0.30
10	32.00	10.16	17.40
14	37.08	15.24	22.48
16	39.62	17.78	25.02
20	44.70	22.86	30.10
24	49.78	27.94	35.18
26	52.32	30.48	37.72
30	57.40	35.56	42.80
34	62.48	40.64	47.88
40	70.10	48.26	55.50
50	82.80	60.96	68.20
60	95.50	73.66	80.90
64	100.58	78.74	85.98

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
E							
D				CHECKED:	UNIT: MM	DESCRIPTION: 2.54mm IDC Ejector Header Type	SIZE A4
C	13-Dec-2013				SCALE:1:1		
B	19-Feb-2013			APPROVAL:	SHEET: 1 / 2	PART NO: 3010-XX-041-11-00	
A	14-Feb-2006				PROJECTION: 		
REV	DATE	FILE	BY				



				RoHS Compliant	
				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15
E				CHECKED:	UNIT: MM SCALE:1:1
D					
C	13-Dec-2013			APPROVAL:	DESCRIPTION: 2.54mm IDC Ejector Header Type
B	19-Feb-2013				PART NO: 3010-XX-041-11-00
A	14-Feb-2006				
REV	DATE	FILE	BY		PROJECTION:
				CnC Tech Industrial Cable and Connector Technology	
				SIZE A4	