



General ordering data

Order No.	1727650000
Part designation	B2L 3.5/8 SN SW
Version	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 8, 180°, Box
EAN	4032248037841
Qty.	50 pc(s).

System parameters

Conductor connection system	Tension clamp connection
Outgoing direction of conductor	180°
Pitch	3.5 mm
Pitch in inch	0.138 inch
No. of poles	8
No. of rows	2
Stripping length	7 mm
L1 in mm	10.5 mm
L1 in inch	0.413 inch
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	PBT
---------------------	-----

Material data

Colour	black
colour chart	Similar to RAL 9011
Insulating material group	IIIa
Flammability class UL 94	V-0
CTI	≥ 200
Contact base material	Copper alloy
Contact surface	tinned

Connectable conductors

Clamping range, min.	0.08 mm ²
Clamping range, max.	1 mm ²
AWG, min.	28
AWG, max.	18
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	1 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.13 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	0.34 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.13 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	0.34 mm ²

DIN IEC rating data

Rated voltage for overvoltage class/pollution severity II/2	250 V
Rated voltage for overvoltage class/pollution severity III/2	125 V
Rated voltage for overvoltage class/pollution severity III/3	80 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2.5 kV
Short-time withstand current resistance	3 x 1s with 77 A

CSA rating data

Rated voltage (Use group D)	50 V
Rated current (Use group D)	5 A
AWG conductor (field wiring), min.	28
AWG conductor (field wiring), max.	18

UL 1059 rating data

Rated voltage (Use group D)	150 V
Rated current (Use group D)	10 A
AWG conductor, min.	22
AWG conductor, max.	16

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-01

Similar products

Order No.	Part designation	Version
1006630000	B2L 3.5/04 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 4, 180°, Box
1920840000	B2L 3.5/04 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 4, 180°, Box
1727560000	B2L 3.5/6 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 6, 180°, Box
1727640000	B2L 3.5/6 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 6, 180°, Box
1727570000	B2L 3.5/8 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 8, 180°, Box
1727580000	B2L 3.5/10 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 10, 180°, Box
1727660000	B2L 3.5/10 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 10, 180°, Box
1727590000	B2L 3.5/12 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 12, 180°, Box
1727670000	B2L 3.5/12 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 12, 180°, Box
1727600000	B2L 3.5/14 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 14, 180°, Box
1727680000	B2L 3.5/14 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 14, 180°, Box

1727610000	B2L 3.5/16 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 16, 180°, Box
1727690000	B2L 3.5/16 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 16, 180°, Box
1727620000	B2L 3.5/18 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 18, 180°, Box
1727700000	B2L 3.5/18 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 18, 180°, Box
1727630000	B2L 3.5/20 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 20, 180°, Box
1727710000	B2L 3.5/20 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 20, 180°, Box
1747850000	B2L 3.5/22 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 22, 180°, Box
1747930000	B2L 3.5/22 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 22, 180°, Box
1747860000	B2L 3.5/24 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 24, 180°, Box
1747940000	B2L 3.5/24 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 24, 180°, Box
1747870000	B2L 3.5/26 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 26, 180°, Box
1747950000	B2L 3.5/26 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 26, 180°, Box
1747880000	B2L 3.5/28 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 28, 180°, Box
1747960000	B2L 3.5/28 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 28, 180°, Box
1747890000	B2L 3.5/30 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 30, 180°, Box
1747970000	B2L 3.5/30 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 30, 180°, Box
1747900000	B2L 3.5/32 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 32, 180°, Box

1747980000	B2L 3.5/32 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 32, 180°, Box
1747910000	B2L 3.5/34 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 34, 180°, Box
1747990000	B2L 3.5/34 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 34, 180°, Box
1747920000	B2L 3.5/36 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 36, 180°, Box
1748000000	B2L 3.5/36 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1 mm ² , Pitch: 3.50 mm, No. of poles: 36, 180°, Box