

Opti-Core™ Fiber Optic Indoor/Outdoor All-Dielectric Cable with Tight Buffered Fibers - Americas

technical information

Panduit® Opti-Core® Indoor/Outdoor All-Dielectric Cable with tight buffered fibers are an integral part of the Panduit end-to-end fiber optic solution, designed to support today's data needs while meeting tomorrow's ever-advancing network requirements. This cable provides water blocking technology, high density, and easy installation in transitional aerial and duct applications and entrance facilities, and the 900µm tight-buffered fibers provides easy connectorization. The tight-buffered fibers surrounded by aramid yarn strength members combine usability indoors and out. Cables with greater than 24 fibers feature a sub-unit design that simplifies fiber identification, provides easy access and routing of the fibers. It also increases cable durability with a dielectric central strength member. Opti-Core® Fiber Optic Indoor/Outdoor Riser (OFNR) and Plenum (OFNP) Rated All-Dielectric Cable with tight buffered fibers are tested in accordance with Telcordia GR-20, Issue 2, GR-409 and with relevant EIA/TIA-455 series FOTPs for fiber optic cable. All multimode and singlemode cable is available in 2, 4, 6, 8, 12, and 24-fiber counts as a "non-subunitized" design and in 36, 48, 72, and 96-fiber counts (144 for Riser) as a "sub-unitized" design. All Opti-Core® fiber cable is RoHS compliant.



application

These cables provide an effective solution for inter-building and building transition applications utilizing field installable connectors. This cable is available in both riser rated and plenum rated version for deployment in any inside plant fire-code application. The UV-resistant outer jacket, coupled with dry water-blocking technology, address environmental concerns for outdoor use.

standards

TIA/EIA-568	ANSI/ICEA S-83-596
ANSI/ICEA S-104-696	CSA 22.2
UL-1666	Telcordia GR-409
NFPA 262	Telcordia GR-20
ROHS Compliant	

construction

900um Tight buffered PVC				
Fiber color code	1 Blue	7 Red	13 Blue with Black tracer	19 Red with Black tracer
	2 Orange	8 Black	14 Orange with Black tracer	20 Black with White tracer
	3 Green	9 Yellow	15 Green with Black tracer	21 Yellow with Black tracer
	4 Brown	10 Violet	16 Brown with Black tracer	22 Violet with Black tracer
	5 Slate	11 Rose	17 Slate with Black tracer	23 Rose with Black tracer
	6 White	12 Aqua	18 White with Black tracer	24 Aqua with Black tracer
Water blocking	Aramid yarns with water blocking capability			
Inner sheath	PVC			
Outer sheath	PVC			

Opti-Core™ Fiber Optic Indoor/Outdoor All-Dielectric Cable with Tight Buffered Fibers - Americas

mechanical properties

Tensile strength (Installation)	E1	Riser: 2 to 12-fibers: 100 lbs (12 fiber is rated for 150 lbs.) 18 to 24-fibers: 300 lbs. 36 to 144-fibers (sub-unitized): 600 lbs. Plenum: 2 to 8-fibers: 100 lbs. 12 to 24-fibers: 150 lbs. 36 to 48-fibers (sub-unitized): 400 lbs. 72 to 96-fibers (sub-unitized): 600 lbs.
Tensile strength (long-term)	E1	Riser: 2 to 12-fibers: 30 lbs. 18 to 24-fibers: 90 lbs. 24 to 144-fibers (sub-unitized): 180 lbs. Plenum: 2 to 8-fibers: 30 lbs. 12 to 24-fibers: 45 lbs. 36 to 48-fibers (sub-unitized): 120 lbs. 72 to 96-fibers (sub-unitized): 180 lbs
Compressive strength (crush)	E3	125 PSI
Impact	E4	Per FOTP 25
Torsion	E7	Per FOTP 85
Kink	E10	Per FOTP 104
Temperature range	F1	Shipping/Storage: (Riser) -40 °F to +176 °F (-40 °C to +80 °C) (Penum) -40 °F to +176 °F (-40 °C to +80 °C) Installation: (Riser) +14 °F to +140 °F (-10 °C to +60 °C) (Penum) +32 °F to +140 °F (0 °C to +60 °C) Operation: (Riser) -40 °F to +176 °F (-40 °C to +80 °C) (Penum) -40 °F to +176 °F (-40 °C to +80 °C)
Water penetration	F5B	No water on free end

physical properties-riser

Fiber Count	Cable O.D. Inches (mm)	Long-Term Bend Radius Inches (cm)	Installation Bend Radius Inches (cm)	Cable Weight Lb./kft. (kg/km)
2	0.19 (4.8)	1.9 (4.9)	3.8 (9.7)	15 (22)
4	0.22 (5.6)	2.2 (5.6)	4.4 (11.2)	19 (28)
6	0.24 (6.0)	2.4 (6.1)	4.8 (12.2)	21 (31)
8	0.25 (6.2)	2.5 (6.4)	5.0 (12.7)	23 (34)
12	0.28 (7.0)	2.8 (7.2)	5.6 (14.3)	30 (45)
24	0.32 (8.1)	5.6 (14.3)	6.4 (16.3)	43 (64)
36	0.66 (16.8)	6.6 (16.8)	13.2 (33.6)	103 (153)
48	0.66 (16.8)	6.6 (16.8)	13.2 (33.6)	140 (209)
72	0.80 (20.3)	8.0 (20.4)	16.0 (40.7)	208 (309)
96	0.95 (24.2)	9.5 (24.2)	19.0 (48.3)	296 (441)
144	1.02 (25.9)	10.2 (25.9)	20.4 (51.9)	347 (516)

Opti-Core™ Fiber Optic Indoor/Outdoor All-Dielectric Cable with Tight Buffered Fibers - Americas

physical properties-plenum

Fiber Count	Cable O.D. Inches (mm)	Long-Term Bend Radius Inches (cm)	Installation Bend Radius Inches (cm)	Cable Weight Lb./kft. (kg/km)
2	0.18 (4.5)	1.8 (4.6)	3.6 (9.2)	9 (13)
4	0.18 (4.6)	1.8 (4.6)	3.6 (9.2)	14 (21)
6	0.20 (5.0)	2.0 (5.1)	4.0 (10.2)	15 (22)
8	0.20 (5.2)	2.0 (5.1)	4.0 (10.2)	18 (27)
12	0.24 (6.1)	2.4 (6.1)	4.8 (12.2)	22 (33)
24	0.30 (7.6)	4.1 (10.5)	8.2 (20.9)	42 (62)
36	0.54 (13.9)	5.4 (13.8)	10.8 (27.5)	132 (196)
48	0.55 (13.9)	5.5 (14.0)	11.0 (28.0)	140 (209)
72	0.65 (16.6)	6.5 (16.6)	13.0 (33.1)	210 (312)
96	0.84 (21.3)	8.4 (21.4)	16.8 (42.7)	345 (514)

ordering information

Example: FSKR512- Fiber, Indoor/Outdoor Tight Buffered Unarmored, Riser Rated, OM2, 12-Fiber

Character	1	2	3	4	5	6	7
Example	F	S	K	R	5	1	2

1 and 2 – Fiber Product

FS = Fiber- OM1, OM2, OS1
FO = Fiber- OM3, OM4

3 – Cable Construction

K - Indoor/Outdoor
Tight Buffered Unarmored

4 – Flame Rating

R - Riser
P - Plenum

5 – Fiber Type

9 = OS1/OS2 9/125µm
6 = OM1 62.5/125µm
5 = OM2 50/125µm
X = OM3 10G 50/125µm
Z = OM4 10G 50/125µm

6 and 7 – Fiber Count

02 = 2-Fiber
04 = 4-Fiber
06 = 6-Fiber
08 = 8-Fiber
12 = 12-Fiber
24 = 24-Fiber
36 = 36-Fiber
48 = 48-Fiber
72 = 72-Fiber
96 = 96-Fiber
1A = 144-Fiber

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2014 Panduit Corp.
ALL RIGHTS RESERVED.
FBDS06--WW-ENG
2/2014