

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

(C) COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-15-012172, RELEASE PRODUCTION VERSION	17AUG2015	GF	SM
	A1	ECR-15-012489, UPDATE NOTE DESCRIPTION	24AUG2015	GF	SM

NOTES :


1. MATERIALS AND FINISH:
- CONTACTS: COPPER ALLOY, FINISH: TIN OVER NICKEL UNDERPLATE
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. WIRE TYPES AND SIZES ACCEPTED
WIRE SIZE: 20AWG SOLID & STRANDED(CONDUCTOR NO:7)
22AWG SOLID & STRANDED(CONDUCTOR NO:7)
24AWG SOLID
TIN-DIPPED FOR ALL STRANDED WIRE
MAX INSULATION OD: 1.75mm MAX.
STRIP LENGTH: 5.5+/-0.3mm
4. PACKAGED IN TAPE AND REEL



FRONT



P/N:2834010-3



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN GEORGE FU 24AUG2015

CHK SHI MING 24AUG2015

APVD XU XIANG 24AUG2015

PRODUCT SPEC

108-137049

APPLICATION SPEC


114-137049

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



MATERIAL



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.20
2 PLC	±0.13
3 PLC	±
4 PLC	±
ANGLES	±

FINISH



NAME

SLIM CONTACT

SIZE

A3

CAGE CODE

-

DRAWING NO

C=2834010

RESTRICTED TO

-

SCALE 12:1

SHEET

1

OF

1

REV

A1