

# LED Lamps and LED Lampholders

LED Lampholders can be supplied with or without lamps

## Colours:

Red, Yellow and Green LEDs  
(High Intensity is standard. Option of extra super bright)

## Voltages:












LEDs are available for direct connection to 2.0/2.2V. or 12Vdc  
For other voltages contact the factory

## To create a catalogue number:

Refer to the 2 columns below (terminal and type)

Then state:

LED colour and voltage and body finish (Black or Chrome)

| TERM                                                                                                                  | TYPE                                                                                                                                         | PANEL & °C                                                                                                                                                                                                                                                                       | DIMENSIONS (mm)                                                                                              |                                                                                                |
|-----------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|
| <b>W</b><br><br>LED fitted           | <b>(W) 1047 00</b><br><br>3mm LED                           |  6.3<br> 6.3max<br> T85       | <br>1.5<br>12.7<br>13.9   | <br>Ø7.6    |
| <b>A</b><br>LED not fitted                                                                                            |                                                                                                                                              |                                                                                                                                                                                                                                                                                  |                                                                                                              |                                                                                                |
| <b>L</b><br><br>LED & Wires fitted   | <b>L 1047 00</b><br><br>3mm LED                            |  6.3<br> 6.3max<br> T85    | <br>1.5<br>12.7<br>13.9  | <br>Ø7.6   |
| <b>W</b><br><br>LED fitted         | <b>(W) 1048 00</b><br><br>5mm LED                         |  8.0<br> 5.5max<br> T85 | <br>2.0<br>10.0<br>14.5 | <br>Ø9.5  |
| <b>A</b><br>LED not fitted                                                                                            |                                                                                                                                              |                                                                                                                                                                                                                                                                                  |                                                                                                              |                                                                                                |
| <b>L</b><br><br>LED & Wires fitted | <b>L 1048 00</b><br><br>5mm LED                           |  8.0<br> 5.5max<br> T85 | <br>2.0<br>10.0<br>14.5 | <br>Ø9.5  |
| <b>W</b><br><br>LED fitted         | <b>(W) 1050 00</b><br><br>5mm LED with focusing reflector |  8.0<br> 7.0max<br> T85 | <br>2.9<br>12.4<br>16.9 | <br>Ø10.0 |
| <b>A</b><br>LED not fitted                                                                                            |                                                                                                                                              |                                                                                                                                                                                                                                                                                  |                                                                                                              |                                                                                                |
| <b>L</b><br><br>LED & Wires fitted | <b>L 1050 00</b><br><br>5mm LED with focusing reflector   |  8.0<br> 7.0max<br> T85 | <br>2.9<br>13.4<br>17.9 | <br>Ø10.0 |