


## Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 3A/125VAC
- Insulation resistance: 100MΩ @ >500VDC
- Dielectric Strength: 500VAC for 1 minute
- Contact resistance: <50mΩ
- Life cycling (full load): 200,000 cycles

**Note:**

- OP: Operating Position
- FP: Free Position
- Pre Travel: FP-OP
- RoHS Compliant

**Mechanical Specifications:**

- Switching timing: non-shorting
- Life cycling (no load): 1,000,000 cycles
- Temperature range: -25~+80°C
- Ambient humidity used: <85% RH
- Operating force: 28±10g
- Travel: Ø.86"

**Materials:**

- Housing, button: 30% glass fiber reinforced PBT, black
- Switch lever: stainless steel
- Switch terminals: brass
- Spring: steel
- Contacts: silver
- Metal contact: phosphor bronze

**Miniature Snap Switch**  
101-1204-EV

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com)

1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-1204-EV](#)