













* COVER TAPE PEELING FORCE:


165°~180°	A
0.1N~1.3N	F

PULL OUT DIRECTION
PEELING SPEED 300MM/MIN



NOTE:

- PACKAGING MATERIAL:
 - COVER TAPE: COMPOSITE OF POLYETHYLENE TEREPHTHALATE (PET)
 - CARRIER: POLYSTYRENE (PS)
 - CARRIER REEL: CORRUGATED FIBER
 - BAG: PET
 - BOX: CORRUGATED FIBER.
- EACH BAG SHALL BE INCLUDED:
*DESICCANT
- PEELING STRENGTH: 0.1~1.3N(1~130 GRAMS)
FOR 12~56mm WIDE CARRIER TAPES
- PEELING SPEED: 300mm/MINUTES.



8.10KG	5.57KG				2-1734858-5~8
7.55KG	5.02KG				2-1734858-1~4
7.50KG	4.91KG	350	4	1400	1-1734858-5~8
7.05KG	4.49KG				1-1734858-1~4
7.10KG	3.88KG				1734858-X
GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN				TE Connectivity	
DIMENSIONS: mm		CHK				NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				MODULAR JACK RJ45/RJ11 TOP ENTRY,SMT TYPE	
0 PLC ± .		PRODUCT SPEC				SIZE CAGE CODE DRAWING NO	
1 PLC ± 0.3		APPLICATION SPEC				RESTRICTED TO	
2 PLC ± 0.2		WEIGHT				A3 00779 C=1734858	
3 PLC ± 0.15		CUSTOMER DRAWING				SCALE	
4 PLC ± .						SHEET 3 of 3	
ANGLES ± 3°						REV A3	
MATERIAL							
FINISH							