






.040 MULTILOCK Connectors (Mark II) **Wire to Wire Applications**

Tab Contact (To be used with cap housing for wire to wire connections.)						
Contact	Wire Range	Wire Ins. Diameter	Material/Finish	Part No.		Hand Tool No. (Instruction Sheet)
				S.T.	L.P.	
.040 Tab  Crimp Specifications:114-5108	0.3~0.5mm ² (AWG#22-20)	Ø1.8-2.0mm	Brass/Pre-tin	173682-1	175063-1	91577-1 (411-5417)

Receptacle Contact (To be used with plug housing.)						
Contact	Wire Range	Wire Ins. Diameter	Material/Finish	Part No.		Hand Tool No. (Instruction Sheet)
				S.T.	L.P.	
.040 Receptacle  Crimp Specifications:114-5094	0.3~0.5mm ² (AWG#22-20)	Ø1.8-2.0mm	Copper Alloy/Pre-tin	173681-1	175062-1	91577-1 (411-5417)
			Copper Alloy/Sel. Gold	173681-2	175062-2	
.040 Receptacle  For an extra-thin jacketed cable Crimp Specifications:114-5162	0.3~0.5mm ² (AWG#22-20)	Ø1.1-1.6mm	Copper Alloy/Pre-tin	175180-1	—	—
			Copper Alloy/Sel. Gold	175180-2	—	

Cap (To be used with .040 tab contact.)	12 Pos.	Plug (To be used with .040 rec.contact.)
Part Number : 1123882-2 		Part Number : 175965-2 

*The material of housing is of PBT, and its color is black.
 *16 pos. is available. (cap P/N : 1473196-1, Plug P/N : 175966-2)