




Passive - 2 wire
16 Channel
Output
GE Fanuc






Passive - 2 wire
16 Channel
Output Fused* w/LED and MOV
GE Fanuc



Passive - 2 wire
16 Channel
Output Fused* w/MOV
GE Fanuc



RS PLC GE9030 16PT 2x8			RS PLC DO W/BFI & MOV		RS PLC DO W/F & MOV	
998189	120 VAC	IC693MDL340	998001	IC693MDL740	996572	IC693MDL740
998064	24 VDC	IC693MDL740, 742				
998069	24 VDC	IC693MDL741				
See Above			24 VDC		24 VDC	
3.0 A per channel / 3.0 A per group of 8 / 6.0 A per module			1.5 A per channel / 3.0 A per group of 8 / 6.0 A per module		1.5 A per channel / 3.0 A per group of 8 / 6.0 A per module	
(1) 1 x 20 pin IDC			(1) 1 x 20 pin IDC		(1) 1 x 20 pin IDC	
No			Yes		No	
0°C...+50°C			0°C...+50°C		0°C...+50°C	
-20°C...+60°C			-20°C...+60°C		-20°C...+60°C	
90 x 70 x 56			123 x 109 x 61		123 x 109 x 61	
#26...14 AWG			#26...14 AWG		#26...14 AWG	
Screw Clamp			Screw Clamp		Screw Clamp	



*5 x 20 mm fuses are required.
Note: Markings vary based on I/O used.

PART NUMBER SELECTION TABLES

Weidmüller