

► [Heatsinks f.cool](#)

► [Cases f.case](#)

▼ [Connectors f.con](#)

► [Sockets](#)

▼ [PCB connectors](#)

■ [Male headers](#)

■ [Female headers](#)

■ [Direct female connector](#)

■ [Jumpers](#)

► [IDC-connectors](#)

► [D-Sub connectors](#)

■ [Brackets for PC](#)


► [Optoelectronic](#)

Jumpers

CAB 5 Z G

for 0.6-0.64 mm wire wrap pins and Ø 0.6-0.7 mm The flexible contacts are shorting two pins. The jumpers can be mounted behind and next to each other.

[add to request](#)



[Features](#)

[Technical Drawing](#)

[Variants](#)

no. of contacts	2
surface contact / contact sleeve	0,5µm Au 1µm Au 5µm Sn
surface of contact	5.0 µm tin
insertion depth	4...5,5mm
nominal current	3 A
nominal voltage	250 V AC
material isolation body	PA 6
temperature range	-40 °C ... +105 °C
grid	5.08 mm
version	closed, hole for probe trip
colour	grey