

CAB CAB PC 604022 G



Sample photo

Order symbol: CAB PC 604022 G
Product nbr: 8113370
Description: Cabinet, PC
Remarks: Latches on the long side

EAN:	6418074020444
El. number:	
Finland:	3424126
Denmark:	8212020281
Italy:	7821065
Sweden:	2539983

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	220	Ingress Protection (EN 60529): IP 65
inch:		23.6	15.7	8.7	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			Germanischer Lloyd (GL)
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Lloyds Register of Shipping (LR)
EKIV 64H		Mounting plate			Europe EN 50298: 1998
EKIV 37		DIN-35 Mounting rail			UL Canada
DS3537OE1		DIN-35 Mounting rail			Gost R
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 64		Front plate			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			

