




REVISION	DATE	DESCRIPTION	PREPARED:	NOTES	TENSILITY 20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com		
A	12/5/2012	Initial release		1. Shell, brass, nickel plated 2. Spring contact, brass, nickel plated 3. Insulator, PBT, black 4. Pin, brass, nickel plated			
A1	3/4/2013	Updated spec format	VERIFIED:	RoHS compliant	SIZE A PART NUMBER 50-00333		
			DIMENSIONS ARE IN MILLIMETERS	Function test: no open, no short circuit, no INT			
			TOLERANCES: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	DESCRIPTION: Connector, dc jack, 4.75x1.7x17.5 mm, molding style	SCALE: 2:1 WEIGHT: SHEET 1 OF 1		