


Tab Contacts Asymmetric

**Tabs 2.8 x 0.8 mm  
with Asymmetric  
Steel Top Spring,  
Mates with  
Junior Power Timer**

**Extraction Tool:**  
Part No. **726544-1**

**Product Specification:**  
108-18063

**Application Specification:**  
114-18051



**Standard Tab Contacts**

| Wire Size<br>Range<br>(mm <sup>2</sup> ) | Insulation Diameter |             | Material<br>and Finish* | Part Numbers  |                   |                 |                   |             |
|------------------------------------------|---------------------|-------------|-------------------------|---------------|-------------------|-----------------|-------------------|-------------|
|                                          | FLK<br>(mm)         | FLR<br>(mm) |                         | Strip<br>Form | Packaging<br>Unit | Loose-<br>Piece | Packaging<br>Unit | Applicator* |
| 0.2-0.5                                  | -                   | 1.1-1.6     | -1 / -2                 | 962882        | 4,500             | 963813          | 500               | x-878609-x  |
| 0.5-1.0                                  | -                   | 1.4-2.1     | -1 / -2                 | 962883        | 4,500             | 963814          | 500               | x-878610-x  |
| 1.5-2.5                                  | -                   | 2.2-3.0     | -1 / -2                 | 962884        | 3,500             | 963815          | 500               | x-878611-x  |

**Tab Contacts with Single Wire Sealing System**

| Wire Size<br>Range<br>(mm <sup>2</sup> ) | Insulation Diameter |             | Material<br>and Finish* | Part Numbers  |                   |                 |                   |             |
|------------------------------------------|---------------------|-------------|-------------------------|---------------|-------------------|-----------------|-------------------|-------------|
|                                          | FLK<br>(mm)         | FLR<br>(mm) |                         | Strip<br>Form | Packaging<br>Unit | Loose-<br>Piece | Packaging<br>Unit | Applicator* |
| 0.2-0.5                                  | -                   | 1.2-1.6     | -1 / -2                 | 962879        | 4,500             | 963810          | 500               | x-878609-x  |
| 0.5-1.0                                  | -                   | 1.4-2.1     | -1 / -2 / -3            | 962880        | 2,500             | 963811          | 500               | x-878618-x  |
| 1.5-2.5                                  | -                   | 2.2-3.0     | -1 / -2 / -3            | 962881        | 2,500             | 963812          | 500               | x-878619-x  |

\*) **Material and Finish:**  
xxx-1 = CuSn, pre-tin plated  
xxx-2 = CuFe, pre-tin plated  
xxx-3 = CuSn, contact area gold plated

♦) The pre- and suffix for the applicators depends on the applied termination equipment.

Additional Finishes on request.