

2.4GHz Universal Whip Antenna

Electrical Specifications

Frequency Range:	2.4GHz
Nominal Impedance:	50 ohm
Maximum Input Power:	50W
Gain:	3 dBi
Polarization:	Omni
Connector:	SMA Knuckle straight-right angle

Mechanical Specifications

Material:	Rugged Antenna
Antenna dimensions:	210 x 15 straight. 185 x 15 right angle
Antenna weight:	30g
Ambient temperature:	-40 °C-+ 60 °C

Order Code: ANT-2.4G

