



SIZE	Part Number	Jack Screw Thread	Packing
25	8655MH2501LF	UNC 4-40	bulk : Qty 60
	8655MH2511LF		individual set 50 sets/carton
	8655MH2502LF	M3	bulk : Qty 60
	8655MH2512LF		individual set 50 sets/carton



NOTE:RoHS INFORMATIONS

-The LF product meets European union Directives and other country regulations as described in GS-22-009
 -The product is not intended to be exposed to a manufacturing solder process
 -Packaging spec:see GS-14-920



JACKSCREW
THREAD

M3



SCALE 1:1

NOTES : for every sizes

Material and finish : Zinc die-cast
 nickel plated
 Cable strain relief : Zinc die-cast
 Jackscrew : Steel,nickel plated
 UNC 4-40 or M3 (see tables)
 Temperature range : -55°C to +125 °C
 Attenuation factor : >40 dB between 10 MHz

Other size details : see on next pages.





Copyright FCI.

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm		
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	M PESSON	2008/02/19	ANGULAR	0.X	±/	size	Scale
Eng	M PESSON	2008/02/19	LINEAR	0.XX	±/	A3	3:2
Chr	P LEGARE	2008/02/19	0° ±/°	0.XXX	±/	ECN	FII-0066
Appr	P LEGARE	2008/02/19	Product family		-	Spec ref	
FCI			Title			dwg no	Rev.
			STRAIGHT METAL HOODS			C-8655-1685C	B
			WITH 2 METAL CLAMPS				
			catalog no			CUSTOMER	sheet 1 of 4

rev	ecn no	dr	date
A	LS08-0058	MPE	2008/02/21
B	F11-0066	APA	2011/05/30


REV C - 2006-03-28

SIZE	Part Number	Jack Screw Thread	Packing
09	8655MH0901LF	UNC 4-40	bulk : Qty 80
	8655MH0911LF		individual set 50 sets/carton
	8655MH0902LF	M3	bulk : Qty 80
	8655MH0912LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS

SIZE	Part Number	Jack Screw Thread	Packing
15	8655MH1501LF	UNC 4-40	bulk : Qty 80
	8655MH1511LF		individual set 50 sets/carton
	8655MH1502LF	M3	bulk : Qty 80
	8655MH1512LF		individual set 50 sets/carton





www.fciconnect.com			surface ISO 1302		- ✓	tolerance std ISO 406 ISO 1101		projection 	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	M PESSON	2008/02/19	ANGULAR	LINEAR	0.X	±/	size	Scale	
Eng	M PESSON	2008/02/19			0.XX	±/	A3	3/2	
Chr	P LEGARE	2008/02/19			0° ±°	0.XXX	±/	ECN	F11-0066
Appr	P LEGARE	2008/02/19	Product family				-	Spec ref	
		title STRAIGHT METAL HOODS WITH 2 METAL CLAMPS				dwg no C-8655-1685C		Rev B	
catalog no		-				CUSTOMER		sheet 2 of 4	





Copyright FCI.

SIZE	Part Number	Jack Screw Thread	Packing
37	8655MH3701LF	UNC 4-40	bulk : Qty 40
	8655MH3711LF		individual set 50 sets/carton
	8655MH3702LF	M3	bulk : Qty 40
	8655MH3712LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS

SIZE	Part Number	Jack Screw Thread	Packing
50	8655MH5001LF	UNC 4-40	bulk : Qty 40
	8655MH5011LF		individual set 50 sets/carton
	8655MH5002LF	M3	bulk : Qty 40
	8655MH5012LF		individual set 50 sets/carton



www.fciconnect.com			surface ISO 1302		- ✓	tolerance std ISO 406 ISO 1101		projection 	mm 
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	M PESSON	2008/02/19	ANGULAR	LINEAR	0.X	±/	size	Scale	
Eng	M PESSON	2008/02/19			0.XX	±/	A3	3/2	
Chr	P LEGARE	2008/02/19			0° ±°	0.XXX	±/	ECN	F11-0066
Appr	P LEGARE	2008/02/19	Product family					Spec ref	
	title	STRAIGHT METAL HOODS				dwg no	C-8655-1685C		Rev
		WITH 2 METAL CLAMPS					B		
		catalog no		-			CUSTOMER	sheet 3 of 4	

REV C - 2006-03-28


PDM: Rev:B

STATUS:Released

Printed: Jun 14, 2011


CABLING INSTRUCTIONS

1- Strip the cable and solder or crimp the wires




SCALE 3:2

2-Put the connector into a half hood and tighten the jacket with a metal clamp




SCALE 3:2

3-To get the electrical continuity between the cable outer conductor and the hood tighten the outer conductor with the other metal clamp as shown



SCALE 3:2

4-Mount the jackscrews, the other half hood and tighten with 2 screws



Copyright FCI.

www.fciconnect.com			surface ISO 1302	- ✓	tolerance std ISO 406 ISO 1101	projection ⊕	mm ↔
			TOLERANCES UNLESS OTHERWISE SPECIFIED				size A3
Dr	M PESSON	2008/02/19	ANGULAR	LINEAR	0.X	±/	Scale 3:2
Eng	M PESSON	2008/02/19			0.XX	±/	
Chr	P LEGARE	2008/02/19	0° ±/°		0.XXX	±/	ECN F11-0066
Appr	P LEGARE	2008/02/19	Product family		-	Spec ref	
Title STRAIGHT METAL HOODS WITH 2 METAL CLAMPS			dwg no C-8655-1685C			Rev. B	
catalog no			CUSTOMER			sheet 4 of 4	