


**FOR REFERENCE
ONLY**




**STEWART
CONNECTOR
SYSTEMS, INC.**

R.D. 2, BOX 2020 GLEN ROCK, PENNSYLVANIA 17327

PART NO.: 940-SP-3066-0B
SIX CONDUCTOR/SIX POSITION LINE CORD MODULE; CLEAR;
FOR OVERSIZED FLAT OR OVAL CABLE; FOR CONDUCTORS
WITH MAXIMUM OUTSIDE DIAMETER OF .038 [.965]

0B- OPEN BACK



**SPECIFICATIONS OF STEWART CONNECTOR'S
MODULAR PLUGS**

CONTACT MATERIAL: 8% PHOSPHOR BRONZE
CONTACT PLATING: 50 MICRO-INCH (1.27 MICRON)
SELECTIVE 24 CARAT HARD GOLD PLATE IN CONTACT AREA
OVER 100 MICRO-INCH (2.54 MICRON) MINIMUM NICKEL PLATE
PER CURRENT SELECTIVE GOLD PLATING REQUIREMENTS.
PLUG MATERIAL: POLYCARBONATE
PLUG TOLERANCES AND DIMENSIONS: COMPLIES WITH F.C.C REQUIREMENTS
ALL OTHER DIM'S ± 0.005 (± 0.127 MM)
DIM'S WITH ** TO BE CENTRAL ABOUT CENTER LINE
FLAME AUTO EXTINGUISH LEVEL: 94-V0 (U.L. RECOGNIZED-FILE
NO. E132408 (N))
OPERATION TEMPERATURE: -40°C TO +125°C
INSERTION/EXTRACTION LIFE: 1000 CYCLES (USING STEWART
CONNECTOR JACKS)
CONTACT RESISTANCE: 10 MILLOHMS MAX. (USING
STEWART CONNECTOR JACKS)
CURRENT/VOLTAGE: 30 VAC/42 VDC AT 1.5 AMPS