

Pen DMM with Non-Contact Voltage Detector

Autoranging MultiMeter with rotary dial

With a retractable tip for safe storage

Features:

- Large 2000 count high contrast LCD display
- Non-Contact Voltage detection with visible and audible alarm
- Autoranging with Data Hold, Range Hold, and Maximum Hold features
- Functions include AC/DC Voltage, Resistance, Continuity and Diode Test
- Auto Power off to conserve battery life
- Overload and low battery indication
- Meets IEC1010-1; CAT III-600V
- Complete with test lead with alligator clips, two 1.5V AAA batteries, and carrying case

Applications:

- AC live circuit detection
- Field Service troubleshooting tool for AC/DC circuits
- R & D and circuit board troubleshooting
- Digital circuitry testing



Built-in Non-Contact Voltage Detector automatically detects a live wire when the red LED is lit



Retractable tip



Specifications	Range	Resolution	Basic Accuracy
Non-Contact Voltage	50 to 600VAC		
DC Voltage	200mV, 2, 20, 200, 600V	0.1mV	±0.7%
AC Voltage	200mV, 2, 20, 200, 600V	0.1mV	±0.8%
Resistance (Ω)	200, 2k, 20k, 200k, 2M, 20MΩ	0.1Ω	±0.8%
Diode Test	1mA @ 1.5V approx		
Continuity Test	Audible beep <50 ohms		
Dimensions	8.2x1.5x1.1" (208x38x29mm)		
Weight	3.9oz (110g)		

Ordering Information:

381676Pen MultiMeter with Non-Contact Voltage Detector

