


[→ Honeywell.com](#) [→ Automation & Control Solutions](#)
[HOME](#)
[ABOUT US](#)
[PRODUCTS & INFORMATION](#)
[NEWS & EVENTS](#)
[SALES & SUPPORT](#)
[LOGIN](#)

Honeywell Sensing and Control



Search



3004 00600002 Thermostats

(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7074)
- Switches (9814)

Technology

- Electromechanical (9357)
- Magnetic (538)
- Microstructure (2328)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...



3004 Series Non-Hermetic Thermostats

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)

Need Help?

[Click here to contact us](#)
[Overview](#)
[Specs](#)
[Documentation](#)
[Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	4.0 A
Voltage	120 Vac
Operating Temperature	-18 °C to 168 °C [0 °F to 335 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	97.8 °C [208 °F]
Close Temperature	5.6 °C [10 °F] max. diff.
Open Tolerance	3.3 °C [6 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Phenolic base with metal closure
Contact Material	Silver
Agency Approvals and Standards	UL
Mounting	HS367 M4x.7 hex cap stud
Series Name	3004

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)