

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

The technical drawing includes three views of the EMT coupling: a side view on the left, a front view on the right, and an isometric view on the far right. The side view shows a height of 6.88 and a base width of .43. The front view shows a top width of 1.00, a base width of .45, and a base height of 3.50. The isometric view shows a height of 3.00 and a base width of 2.31.

6.88

1.00

3.50

3.00

2.31


.43

.45

4.20

NOTES:

1. OPERATIONAL TEMPERATURE RANGE: -40°F (-40°C) TO 140°F (60°C)
2. STORAGE TEMPERATURE RANGE: -40°F (-40°C) TO 250°F (120°C)
3. CAUTION: TOUCHING METAL AT EXTREME TEMPERATURES CAN CAUSE BURNS AND OTHER INJURIES



1. OPERATIONAL TEMPERATURE
RANGE: -40°F (-40°C) TO
140°F (60°C)
2. STORAGE TEMPERATURE
RANGE: -40°F (-40°C) TO
250°F (120°C)
3. CAUTION: TOUCHING METAL
AT EXTREME TEMPERATURES
CAN CAUSE BURNS AND
OTHER INJURIES

										CAD FILENAME/LAYERS				I400I9AC_DC_C I0893/00A			
										PANDUIT CORP. TINLEY PARK, ILLINOIS							
										PSL - HD3 CUSTOMER DRAWING							
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (,.XXX) ± .025 (.XX) ± .05 ANGLES ± 5°				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY BSW		MAT'L; STEEL		SCALE 2:5			
0	1/27/11	BSW		DRAWING RELEASE			6291				DATE 01/27/11			DRAWING NO. C10893		DWG SIZE A	
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP				CHK'D		