



UNIT: mm




CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 **PA** AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V



⑥	PE BAG	1/5	CLEAR SIZE: 360*380*0.05mm PRINT BLACK "MADE IN CHINA" + "5PCS"
⑤	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
④	TIE	2	WHITE L=120mm
③	OUT JACKET	12g	BEIGE (1V-29#) PVC-40P (MOULD NO: WM-40)
②	CABLE	1	BEIGE (1V-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=5000±20
①	CONN	2set	USB A MALE SHELL-NICKEL PIN G/F INSULATION COLOR WHITE 3PCS TYPE
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1020-BE-00500
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	