

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Spring centre contacts for good electrical contact with large solder buckets.
- Internal cable clasp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification
- Attractive body styling.
- Maximum cable size 5.5mm



Ratings 5A at 200 Vdc/150 Vac max.

Insulation resistance – 100MΩ at 500 Vdc

Mechanical Properties

Centre contact	Brass, silver plated
Ground contact	Brass, nickel plated
Insulation	Noryl SE1
Cable clamp	Brass, silver plated
Spring	Spring Steel
Cap	nickel plated
	Brass, nickel plated

Dimensions



Deltron Part No.	Description
340-0000	NICKEL PLATED
340-0100	NICKEL PLATED (BLACK ID RING)
340-0200	NICKEL PLATED (BLUE ID RING)
340-0500	NICKEL PLATED (RED ID RING)
340-0600	NICKEL PLATED (WHITE ID RING)
340-0700	NICKEL PLATED (YELLOW ID RING)

CONVERTED FROM PS0360 ISS2 (14.01.94) IN JAN 2003

DrgnNo 340 SERIES	TITLE PROFESSIONAL PHONO LINE SOCKET				ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES	
-------------------	--------------------------------------	--	--	--	---	--



ISS 2

GENERAL SPECIFICATION
FOR 340 SERIES

CUSTOMER

Aprvd Date 05/02/03

Aprvd By MC

Drwn by BS

Scale: NTS

Sheet 1 / 1

