

CLASSIC TORQUE WRENCHES

TORQUE WRENCH

- Length independent mechanism
- Push through reversible mechanism
- Retractable adjustment mechanism avoids accidental adjustment
- Accurate to $\pm 4\%$
- Complies with ISO 6789
- Supplied in sturdy plastic storage case

	Size	Size	EAN	Price
AVT100A	2.5-11Nm	3/8"	5024344005120	
AVT300A	5-33Nm	3/8"	5024344005137	
AVT600	12-68Nm	3/8"	5024344005144	
EVT1200A	12-135Nm	1/2"	5024344009074	
EVT2000A	50-225Nm	1/2"	5024344009081	
EVT3000A	70-330Nm	1/2"	5024344009104	
EVT600A	12-68Nm	1/2"	5024344009111	
GVT8400	480-940Nm	1"	5024344009678	
HVT5000	140-560Nm	3/4"	5024344934406	
HVT7200	200-810Nm	3/4"	5024344010902	



Storage

Wrenches

Ratchets-Sockets

Screwdrivers

Torque control

Pliers

Hammers - Chisels -
Punches

Sawing - Cutting

Lighting - Pipework -
Maintenance

Electricity -
Electronics

Automotive Tools


Classic Torque Wrench Ranges

Ref.	Square drive	N.m															
		2.5	5	10	20	33	50	70	100	135	200	225	300	330	480	720	940
AVT100A	3/8	2.5	5	10													
AVT300A																	
AVT600																	
EVT600A	1/2																
EVT1200A																	
EVT2000A																	
EVT3000A																	
HVT5000	3/4																
HVT7200																	
GVT8400	1																



Scale Divisions

Series	N.m	Kg.m	lbf.in	lbf.ft
100	0.5	0.1	10.0	1.0
300	1.0	0.1	10.0	1.0
600	2.0	0.2	20.0	2.0
1200	5.0	1.0	50.0	2.0
2000	5.0	1.0	50.0	2.0
3000	10.0	1.0	100.0	10.0
5000	10.0	-	100.0	10.0
8400	10.0	-	-	10.0



A and E series adjustable torque wrenches are supplied in a sturdy plastic storage case.