


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
J	—	P	LTR	DESCRIPTION	DATE
		O		RELEASED FJA0-0444-03	23JUL03
					AY
					KB



- JUMPER LENGTH "L" IS FROM 12.7 MIN. TO 609.6 MAX.
- RECOMMENDED THROUGH HOLE DIA DIMENSION FOR P.C.BOARD: $\phi 0.94 \pm 0.025$
THROUGH HOLE PITCH TOLERANCE: ± 0.127
- ANOTHER SPECIFICATION SHOULD BE ESTABLISHED
IN CASE OF DEVIATION FROM THIS SPECIFICATION.
- WHEN N IS GREATER THAN 31, PCN INSERTION IS SUBJECT TO HAVE DIFFICULTY.
- DIMENSIONS OF LEAD POSITION ARE FOOT OF LEAD.

- ジャンパー長さ"L"は、最小12.7から、最大609.6まで。
- プリント基板スルーホール径： $\phi 0.94 \pm 0.025$ また、
スルーホールピッチ公差は、 ± 0.127 である。(推奨)
- 本仕様から逸脱する場合は、必ず仕様打合わせを行うこと。
- N31以上製品は、プリント基板挿入性が悪い場合がある。
- リード位置寸法は、リード根元部寸法とする。

2.54	38.1	7	-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			FSN-215A-7=JUMPER	7-1447184-3	A
P	L	N	PART NAME	PN	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 英 MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
MATERIAL 材料	FINISH 仕上
-	-

DWN	A.YAMAGUCHI	22JUL03
CHK	K.BETSUI	23JUL03
APVD	K.BETSUI	23JUL03
PRODUCT SPEC	製品規格	108-78002
APPLICATION SPEC	取付適用規格	-
WEIGHT	-	-

WIRE RANGE 包含電線斷面積		INSULATION DIA 被覆外徑	
tyco		Tyco Electronics AMP K.K.	
Electronics		Kawasaki, Japan	
NAME 名稱			
FLEX STRIP JUMPER P2.54L38.1N7			
SIZE	CAGE CODE	DRAWING NO 番號	RESTRICTED TO
A3	00779	C-1717663	—
SCALE 尺 度		SHEET	REV
1:1		1 OF 1	0